




3" WSP Pump Curve

The WSP is Exclusively
Distributed by EPG Pumps
1800 351 755
www.weirselfprimer.com.au



Suction: 3"
Discharge: 3"
Impeller Diameter: 8.75"
Max. Solid Sphere: 2.50"

REPRIMING LIFTS	
RPM	FEET
650	5
750	6
850	8
950	10
1050	13
1150	16
1250	18
1350	19
1450	20
1550	21
1650-1750	22
1850-2150	25

Determine NPSHR prior to using repriming table. Do not use available suction lifts.

Clear Water Performance

$$BHP = \frac{GPM \times FT \times SG}{3960 \times Efficiency}$$

$$KW = \frac{M^3 / HR \times M \times SG}{367 \times Efficiency}$$

© Copyright
All rights reserved **WEIR SPECIALTY PUMPS**

Certified tests are performed using Hydraulic Institute acceptance level B.

FEB. 2006

**RPM
VARIABLE**

WSP3A